

Dental Suction Machine Vacuum System Support 2 Or 3 PCS Dental Chair Units



Number Of Dental Chair	Voltage	Power (W)	Vacuum (kpa)	Air Flow (L/min)	Inlet/Drain Pipe Diameter(mm)	Product size (cm)	Packing size (cm)	Gross weight (kg)
2pcs	220V-50Hz/110V-60Hz	550W	≥1.1Kpa	400L/Min	32mm	38x34x60cm	45x45x65cm	42kg
3pcs	220V-50Hz/110V-60Hz	750W	≥1.2Kpa	600L/Min	32mm	38x34x60cm	45x45x65cm	43kg

Ambient conditions :

Ambient Temperature $+5^{\circ}\text{C} \sim +40^{\circ}\text{C}$

Relative Humidity $\leq 80\%$

The surrounding air must be free of caustic substances.

It cannot exceed 2000 meters above sea level.

Operation modes: intermittent operation mode and continuous operation mode

Relative humidity: $\leq 95\%$

Atmospheric pressure: $500\text{hPa} \sim 1060\text{hPa}$

Circuit diagram: